



POWER-ALL®

WIRELESS COMPATIBILITY CHART

| BRAND | MODEL | PA-9 COMPATIBLE | ADDITIONAL REQUIREMENTS/NOTES |
|-----------------------|--------------------|---------------------------------|---------------------------------|
| AUDIO TECHNICA | 1800 Series | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | 3000 Series | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | 2000 Series | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | 700 Series | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | 200 Series Freeway | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | Pro Series 3 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | Pro Series 5 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | ATR 7000 Series | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | System 10 Stompbox | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | System 10 Digital | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | System 9 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | System 8 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | ATR288W | Yes* | Cable Red |
| | Pro 88W | Yes* | Cable Red |
| GALAXY AUDIO | AS-900 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | AS-1000 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | AS-1100 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | AS-1500 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | DHT | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | TRC | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | PSE | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | ECM | Yes* | Iso-Pump set to 12VDC/Cable Red |
| LINE 6 | G30 | Yes | |
| | G50 | Yes | |
| | G55 | Yes | |
| | XD-V35 Reciever | Yes | |
| | XD-V75 Reciever | Yes | |
| NADY | Encore I | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | Encore II | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | Encore Duet | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | Encore 200 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | U-33B | Yes* | Iso-Pump set to 18VDC/Cable Red |
| SAMSON | Airline Synth | Yes* | Iso-Pump set to 18VDC/Cable Red |
| | Airline 77 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | Stage Series | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | Airline | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | UMI/77 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| SHURE | BLX | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | SLX | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | ULX | Yes* | Iso-Pump set to 18VDC/Cable Red |
| | GLX-D | Yes* | |
| | PGX-D | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | T3 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | T4V | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | T4G | Yes* | Iso-Pump set to 12VDC/Cable Red |
| | T88 | Yes* | Iso-Pump set to 12VDC/Cable Red |
| LX88 | Yes* | Iso-Pump set to 12VDC/Cable Red | |

DISCLAIMER:

The Godlyke Power-All® Power Compatibility Chart should be used for general reference purposes only.

Please check the manufacturer's specifications for each of your wireless units before connecting them to the Power-All® or Power-All® accessories

Please contact us directly at info@godlyke.com if any of the information listed in this chart is unclear to you

Godlyke, Inc. assumes no responsibility for items damaged due to improper connection to the Power-All®